

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 1 of 8

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

SK-2

**1.2. Relevant identified uses of the substance or mixture and uses advised against****Use of the substance/mixture**

Grease

Reserved for industrial and professional use.

**Uses advised against**

The product is only to be used for the intended application.

**1.3. Details of the supplier of the safety data sheet**

Company name:	Harmonic Drive SE	
Street:	Hoenbergstraße 14	
Place:	D-65555 Limburg	
Telephone:	+49 6431 5008-0	Telefax: +49 6431 5008-119
e-mail:	info@harmonicdrive.de	
e-mail (Contact person):	customercare@harmonicdrive.de	
Internet:	www.harmonicdrive.de	

**1.4. Emergency telephone number:**Medical emergency information in case of poisoning: Poison Information Centre  
Mainz - 24h - Tel.: +49 (0) 6131 19240 (Advice in German or English)**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Regulation (EC) No. 1272/2008**

This mixture is not classified as hazardous in accordance with Regulation (EC) No. 1272/2008.

**2.2. Label elements****Regulation (EC) No. 1272/2008****Special labelling of certain mixtures**

EUH066	Repeated exposure may cause skin dryness or cracking.
	7 % of the mixture consists of ingredient(s) of unknown acute toxicity.

**2.3. Other hazards**

Although not classified as "combustible" (based on flash point and ignition properties) this product can be made to burn and will serve as a fuel source for a fire. Thermal decomposition can lead to harmful gases and vapours. Special danger of slipping by leaking/spilling product.

The components in this mixture do not meet the criteria for classification as PBT or vPvB.

**SECTION 3: Composition/information on ingredients****3.2. Mixtures****Chemical characterization**

The mixture does not contain any dangerous ingredients.

**SECTION 4: First aid measures****4.1. Description of first aid measures****General information**

First aider: Pay attention to self-protection!

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 2 of 8

**After inhalation**

Remove affected person from the danger area and lay down. Provide fresh air. If victim is at risk of losing consciousness, position and transport on their side. In case of breathing difficulties administer oxygen. In case of troubles or persistent symptoms, consult an doctor/physician.

**After contact with skin**

After contact with skin, wash immediately with plenty of water and soap. Change contaminated clothing. In case of skin irritation, consult a physician.

**After contact with eyes**

Remove contact lenses. In case of contact with eyes, rinse immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart. In case of troubles or persistent symptoms, consult an ophthalmologist.

**After ingestion**

Rinse mouth, spit liquid again. Do NOT induce vomiting. Let water be drunken in little sips (dilution effect). Seek medical attention if problems persist. Caution if victim vomits: Risk of aspiration!

**4.2. Most important symptoms and effects, both acute and delayed**

Prolonged or repeated skin contact may cause removal of natural fat from the skin resulting in dermatitis (skin inflammation).

**4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptomatically.

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media**

Co-ordinate fire-fighting measures to the fire surroundings.  
Carbon dioxide (CO<sub>2</sub>). Foam. Extinguishing powder. Water fog.

**Unsuitable extinguishing media**

High power water jet.

**5.2. Special hazards arising from the substance or mixture**

In case of fire may be liberated: Carbon monoxide. Carbon dioxide (CO<sub>2</sub>). Sulfur oxides.  
Although not classified as "combustible" (based on flash point and ignition properties) this product can be made to burn and will serve as a fuel source for a fire. Sealed containers may melt, leak, burst or explode, releasing contents and spreading fire, if exposed to extreme heat.

**5.3. Advice for firefighters**

If necessary use self-contained breathing apparatus and protective clothing.

**Additional information**

Do not allow to enter into surface water or drains. Use water spray jet to protect personnel and to cool endangered containers.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures****General advice**

Consider the usual precautions for handling chemicals. Avoid contact with skin, eyes and clothes. Wear personal protection equipment. Keep away from sources of ignition - No smoking. Take action to prevent static discharges.

**6.2. Environmental precautions**

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil.

**6.3. Methods and material for containment and cleaning up****For containment**

Take up mechanically, placing in appropriate containers for disposal. Treat the recovered material as

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 3 of 8

prescribed in the section on waste disposal.

**For cleaning up**

Clean contaminated articles and floor according to the environmental legislation.

**6.4. Reference to other sections**

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

**SECTION 7: Handling and storage****7.1. Precautions for safe handling****Advice on safe handling**

High slip hazard because of leaking or spilled product. Provide adequate ventilation. Avoid contact with skin, eyes and clothes. Keep away from sources of ignition - No smoking. Take action to prevent static discharges.

**Advice on general occupational hygiene**

Avoid contact with skin, eyes and clothes. Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

**Further information on handling**

When using do not eat, drink, smoke, sniff.

**7.2. Conditions for safe storage, including any incompatibilities****Requirements for storage rooms and vessels**

Keep container tightly closed. The storage rooms must be suitable for storing chemical and flammable products.

**Further information on storage conditions**

Keep away from: Heat sources, open flames and other ignition sources. Protect from sunlight. Store in a well-ventilated place.

**7.3. Specific end use(s)**

Grease

Reserved for industrial and professional use.

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Additional advice on limit values**

Currently there are no exposure limits available.

**8.2. Exposure controls****Appropriate engineering controls**

Provide for sufficient ventilation and punctiform suction at critical points.

**Individual protection measures, such as personal protective equipment****Eye/face protection**

Tightly sealed safety glasses.

**Hand protection**

Protect skin by using skin protective cream. In case of prolonged or frequently repeated skin contact: Wear chemically resistant gloves.

Suitable material: NBR (Nitrile rubber). PVC (Polyvinyl chloride).

penetration time (maximum wearing period): >480 minutes

For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

**Skin protection**

Full cover clothing covering arms and legs. Change contaminated clothing.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 4 of 8

**Respiratory protection**

Usually no personal respiratory protection necessary. If technical exhaust or ventilation measures are not possible or insufficient, respiratory protection must be worn. The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product. If the concentration is exceeded, self-contained breathing apparatus must be used.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Physical state: liquid  
Colour: dark green  
Odour: like: Mineral oil

**Changes in the physical state**

Melting point/freezing point: no data available  
Boiling point or initial boiling point and boiling range: no data available  
Sublimation point: no data available  
Softening point: no data available  
Flash point: >160 °C

**Flammability**

Solid/liquid: no data available  
Gas: no data available

**Explosive properties**

no data available

Lower explosion limits: no data available  
Upper explosion limits: no data available  
Auto-ignition temperature: no data available

**Self-ignition temperature**

Solid: no data available  
Gas: no data available

Decomposition temperature: no data available

pH-Value: no data available

Viscosity / dynamic: no data available

Viscosity / kinematic:  
(at 40 °C) >20 mm<sup>2</sup>/s

Water solubility: practically insoluble

**Solubility in other solvents**

no data available

Partition coefficient n-octanol/water: no data available

Vapour pressure: no data available

Density (at 25 °C): 0,91 g/cm<sup>3</sup>

Relative vapour density: no data available

**9.2. Other information**

Oxidizing properties  
no data available

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 5 of 8

Solvent separation test:

no data available

Solvent content:

no data available

**Further Information**

no data available

**SECTION 10: Stability and reactivity****10.1. Reactivity**

No dangerous reactivity under regular conditions.

**10.2. Chemical stability**

The product is stable under regular conditions.

**10.3. Possibility of hazardous reactions**

No dangerous reactions to be expected if used properly.

**10.4. Conditions to avoid**

Heat sources, open flames and other ignition sources.

**10.5. Incompatible materials**

Oxidizing agents, strong. Acid. Permanganates. halogens.

**10.6. Hazardous decomposition products**

In case of fire may be liberated: Carbon monoxide. Carbon dioxide. Sulfur oxides. Irritating/poisonous gasses and vapours.

**SECTION 11: Toxicological information****11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008****Acute toxicity**

Based on available data, the classification criteria are not met.

**Irritation and corrosivity**

Based on available data, the classification criteria are not met.

Frequently or prolonged contact with skin may cause dermal irritation. Repeated exposure may cause skin dryness or cracking.

**Sensitising effects**

Based on available data, the classification criteria are not met.

**Carcinogenic/mutagenic/toxic effects for reproduction**

Based on available data, the classification criteria are not met.

**STOT-single exposure**

Based on available data, the classification criteria are not met.

**STOT-repeated exposure**

Repeated exposure may cause skin dryness or cracking.

**Aspiration hazard**

Based on available data, the classification criteria are not met.

**11.2. Information on other hazards****Endocrine disrupting properties**

no data available

**SECTION 12: Ecological information****12.1. Toxicity**

no data available

**12.2. Persistence and degradability**

no data available

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 6 of 8

**12.3. Bioaccumulative potential**

No data available.

**12.4. Mobility in soil**

No data available.

**12.5. Results of PBT and vPvB assessment**

The components in this formulation do not meet the criteria for classification as PBT or vPvB.

**12.6. Endocrine disrupting properties**

no data available

**12.7. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods****Disposal recommendations**

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.  
Empty containers must be recycled, reused or disposed of by qualified or licensed companies in accordance with the applicable regulations.

**List of Wastes Code - residues/unused products**

070699 WASTES FROM ORGANIC CHEMICAL PROCESSES; wastes from the MFSU of fats, grease, soaps, detergents, disinfectants and cosmetics; wastes not otherwise specified

**List of Wastes Code - used product**

070699 WASTES FROM ORGANIC CHEMICAL PROCESSES; wastes from the MFSU of fats, grease, soaps, detergents, disinfectants and cosmetics; wastes not otherwise specified

**Contaminated packaging**

Handle contaminated packages in the same way as the substance itself.  
Recommended cleaning agent: Water (with cleaning agent)

**SECTION 14: Transport information****Land transport (ADR/RID)**

<b><u>14.1. UN number or ID number:</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.2. UN proper shipping name:</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.3. Transport hazard class(es):</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.4. Packing group:</u></b>	No dangerous good in sense of this transport regulation.

**Inland waterways transport (ADN)**

<b><u>14.1. UN number or ID number:</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.2. UN proper shipping name:</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.3. Transport hazard class(es):</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.4. Packing group:</u></b>	No dangerous good in sense of this transport regulation.

**Marine transport (IMDG)**

<b><u>14.1. UN number or ID number:</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.2. UN proper shipping name:</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.3. Transport hazard class(es):</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.4. Packing group:</u></b>	No dangerous good in sense of this transport regulation.

**Air transport (ICAO-TI/IATA-DGR)**

<b><u>14.1. UN number or ID number:</u></b>	No dangerous good in sense of this transport regulation.
<b><u>14.2. UN proper shipping name:</u></b>	No dangerous good in sense of this transport regulation.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 7 of 8

**14.3. Transport hazard class(es):** No dangerous good in sense of this transport regulation.**14.4. Packing group:** No dangerous good in sense of this transport regulation.**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: No

**14.6. Special precautions for user**

No special precautions known.

**14.7. Maritime transport in bulk according to IMO instruments**

not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Information according to 2012/18/EU (SEVESO III): Not subject to 2012/18/EU (SEVESO III)

**Additional information**

Regulation (EC) No. 648/2004 (Detergents regulation): not applicable

Regulation (EC) No. 1005/2009 on substances that lead to the depletion of the ozone layer: not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants: not applicable

Regulation (EC) No 649/2012 of the European Parliament and of the Council concerning the export and import of dangerous chemicals: This mix contains no chemicals that are subject to the export notification procedures (annex 1).

This mixture contains the following substances of very high concern (SVHC) which are included in the Candidate List according to Article 59 of REACH: none

This mixture contains the following substances of very high concern (SVHC) which are subject to authorisation according to Annex XIV of REACH: none

**National regulatory information**

Water hazard class (D): 1 - slightly hazardous to water

**Additional information**

Observe in addition any national regulations!

**15.2. Chemical safety assessment**

Chemical safety assessments for substances in this mixture were not carried out.

**SECTION 16: Other information****Changes**

Version 1,00 - 23.11.2021 - first creation

**Abbreviations and acronyms**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

BlmSchV (Fed.Imm.Prot.Act): Directive on the Implementation of the Federal Immission Protection Act

CAS: Chemical Abstracts Service

DIN: Norm of the Deutsche Institut für Normung (German Institute for Standardization)

EC: Effective Concentration

EG: European Community (Europäische Gemeinschaft)

EN: European Norm

IATA: International Air Transport Association

IBC Code: International Code for the Construction and Equipment of ships carrying Dangerous Chemicals in Bulk

ICAO: International Civil Aviation Organization

IMDG: International Maritime Code for Dangerous Goods

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**SK-2**

Revision date: 23.11.2021

Product code: HD-004

Page 8 of 8

ISO: Norm of the International Standards Organization  
CLP: Classification, Labeling, Packaging  
IUCLID: International Uniform Chemical Information Database  
LC: Lethal concentration  
LD: Lethal dose  
log Kow: Octanol/water partition coefficient  
MARPOL: Maritime Pollution Convention = Convention for the Prevention of Maritime Pollution from Ships  
OECD: Organisation for Economic Co-operation and Development  
PBT: Persistent, bio-cumulative, toxic  
RID: Regulation Concerning the International Transport of Dangerous Goods by Rail  
TRGS: Technische Regeln für Gefahrstoffe  
UN: United Nations  
VOC: Volatile Organic Compounds  
vPvB: very persistent and very bio-cumulative  
VwVwS: Administrative Regulation for Water Pollutants  
WGK: German Water Hazard Class  
GHS: Globally Harmonized System of Classification and Labelling of Chemicals  
EINECS: European Inventory of Existing Commercial Chemical Substances  
ELINCS: European List of Notified Chemical Substances  
DNEL: Derived No Effect Level  
PNEC: Predicted No Effect Concentration  
TLV: Threshold Limiting Value  
STOT: Specific Target Organ Toxicity  
AwSV: Ordinance on Installations for Handling Substances Hazardous to Water

**Relevant H and EUH statements (number and full text)**

EUH066 Repeated exposure may cause skin dryness or cracking.

**Further Information**

The information given in this safety data sheet is to describe the product's safety regulations. It is not for guaranteeing certain characteristics and is based on today's knowledge. The safety data sheet was generated upon information of pre-suppliers by:

assesio AG, Ottostraße 1, 63741, Aschaffenburg, Germany

Phone: +49 (0)6021 - 1 50 86-0, Fax: +49 (0)6021 - 1 50 86-77, E-Mail: eu-sds@assesio.eu, www.assesio.eu

*(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)*